
## TECHNICAL SPECIFICATION

Туре	RF Fractional Needling
Light Source	Radio Frequency
Control Panel	10.4" Touch Screen
Language	English Standard. Others optional
Therapy Probe	12p, 24p, 40p, Nano Crystal Head
Power	10-300W
Depth	0.5-7mm
Output Frequency	4MHZ
Electrical Voltage	AC110V-230V + 10% 50HZ-60HZ

### ELEVATE YOUR INCOME



\*Based on a 7-day working week over 52 weeks and an average treatment price of £600



# Unlock radiant skin, One fraction at a time with






W W W . L U M I A E S T H E T I C D E V I C E S . C O M

DESIGNED AND DEVELOPED BY UK EXPERTS IN THE UNITED KINGDOM

# LUMI DERMA

LUMI | DERMA combined 2-in-1 device merges Micro-needling with Radio Frequency (RF) technology, marking a major leap in skincare treatments. This cutting-edge device integrates the mechanical advantages of micro-needling with the thermal benefits of RF energy, providing a thorough solution for various skin issues.





W W W . L U M I A E S T H E T I C D E V I C E S . C O M



LUMI DERMA

The LUMI | DERMA is a cutting-edge non-surgical device that merges the advantages of micro-needling with radio-frequency technology.

Featuring ultra-fine, insulated, and adjustable needles, it is designed to safely and effectively treat all skin types and address a variety of skin concerns at different depths, including:

Surgical Scar Reduction

Fine Lines and Wrinkles

Hyperpigmentation

Stretch Marks

Pitted Skin

Remodelling Collagen

Deep Scar Repair

Sculpting and Tightening

UMI | DERMA BENEFITS



#### Two Treatments in One

Micro-needling gently creates tiny punctures in the skin while delivering radio-frequency energy at controlled temperatures of 55-65°C. This dual-action process activates the body's natural wound-healing response, promoting the production of new collagen and elastin.

#### Insulated Needles

Each micro-needle is surrounded by insulation, ensuring that heat is emitted solely from the tip. This precise heating targets the lower layers of the skin, safeguarding the epidermis and making the treatment safer for individuals prone to hyperpigmentation.

#### **Multiple Tip Sizes**

Each device includes a selection of four interchangeable tips of varying sizes, making it possible to handle a broad spectrum of areas. These include small tip: 12 needles, a medium tip: 24 needles and large needles: 40, and an added bonus RF nano-probe.

#### Bonus Mode

**Original Burst Mode:** Deep segmented subcutaneous heating technology. Multi-level fixed-point superposition treatment simultaneously, ensuring uniform and stable energy delivery.

#### Precision Control

Incorporating a built-in step control feature enables precise and consistent needle insertion, enhancing patient comfort while minimizing the risk of epidermal damage and ensuring minimal downtime.

#### Vacuum Technology

The LUMI | DERMA employs vacuum technology to elevate the treatment area, stabilizing the micro-needles and enabling safer and more precise treatment depths. This is especially advantageous for delicate areas.

#### Lightweight Applicator

Designed with a lightweight and ergonomic build, the applicator enhances patient comfort and simplifies

#### 15-inch LED Touch Screen

Experience a user-friendly interface with a large 15-inch LED touch screen featuring magnetic mounting and pre-set specifications for added convenience.

#### Crafted in the UK

The LUMI | DERMA is meticulously designed by our team in the UK, without compromising on specifications. Its advanced technical capabilities and sleek modern design combine seamlessly, ensuring you have access to a device that sets a new standard.